


MADE IN GERMANY



ANAREX (-DS) 2.0

Multigas Analyzer

#2-N21-N22-E50-E40

CO₂ 100 Vol.% / CH₄ 100 Vol.% / O₂ 25 Vol.% /
H₂S 5000 ppm

Product features:

- High stable measuring performance
- Easy operation via touch screen
- Simple sensor calibration
- Standard 19 inch 3HE rack
- Analog and digital output
- Low maintenance and high durability
- High selectivity and measuring accuracy
- Long-term stability and very low drift
- Low detection limit and T90 time



The **ANAREX** product family impresses with its stable high-precision measuring performance, intuitive operation and easy calibration. Designed as a 19-inch multi-gas analyzer, the **ANAREX** is available even with two gas streams as **ANAREX-DS** (double stream) as two in one solution. **ANAREX** gas analyzers are primarily based on the NDIR sensors of the **FLOW^{EVO}** and **SILAREX** series, however, they can be supplemented with several technologies like NDUV, TCD, TDLS, EC,PID, paramagnetic and photoacoustic as well as several other.

smartGAS Mikrosensorik GmbH

Huenderstrasse 1, 74080 Heilbronn, Germany

T +49 (0) 7131 797553-0

sales@smartgas.eu www.smartgas.eu

T +

smartGAS Sensor Technology Co., Ltd

Building 16, No. 59 Jiangnan Rd. CEDZ Changshu, Jiangsu, China

86 (0) 512-83380880

info@smartgas-cn.com www.smartgas-cn.com

General features

Release date: 25. Sep 2024

Multi Gas Analyzer

Gas Streams:	1	
Gas supply:	Flow Mode 1/8" NPTF	
Mounting dimensions:	Standard 19" 3 U	
User Interface:	Touch panel, 5.6" TFT	
Gas Inlet Flow	0.4 .. 0.8 L/min (Flow fluctuations ≤0.02 L/min)	
Inlet Gas Temp.	5 .. 35 °C	
Inlet Gas Pressure	116 kPa (max)	
Moisture in Gas	inlet gas dew point: 5 °C ±0.1 °C	
Dust in gas flow	100 µg/m ³ , ≤ 1µm	
Warm-up time (full specification):	< 30 minutes	
Flow Meter	1	
Internal Gas Tubing	PU (certified)	
Zero Calibration Gas	Stream 1 : Nitrogen	Stream 2 : -/-
Span Calibration Gas Background	Stream 1 : Nitrogen	Stream 2 : -/-

Measuring*

Response time (t90)**:	< 30 s					
Gas	Technology	Range	Linearity Error	Display	C.C**	P.C***
1 CO ₂	NDIR (Biogas)	0 .. 100 Vol.%	±1 %[FS]	XXX.x	/	no
2 CH ₄	NDIR (Biogas)	0 .. 100 Vol.%	±1 %[FS]	XXX.x	/	no
3 O ₂	EC	0 .. 25 Vol.%	±2 %[FS]	XX.x	/	no
4 H ₂ S	EC	0 .. 5000 ppm	±2 %[FS]	XXXX	/	no
5	Cross Sensitivities to O ₂ :		Cross Sensitivities to H ₂ S :			
CO ₂	0.1 Vol.% @ 5 Vol.%		NO	< 3 ppm	@ 50 ppm	
H ₂	-0.2 Vol.% @ 2000 ppm					

Electrical parameters

Supply voltage / Power Connector	198~242V AC, 50/60 Hz / EN60320 C1
Analog (0)4..20mA Output	Range adjustable by user
Case Protection Level	IP42 (EN60529)
Package Dimensions	577mm*512mm*255mm

Climatic conditions

Operating temperature:	5 °C .. 45 °C
Storage temperature:	-20 .. + 60 °C
Air pressure:	760 .. 1160 hPa
Ambient humidity:	0 .. 95 % relative humidity (not condensing)

Accessories to be ordered separately :

Power Cable:	Refer to the requirement of country
Gas Connections (one Set : Inlet/Outlet)	Stainless Steel: 1/8" 1/4" 10mm 6mm Rubber Tube: 6mm PTFE: 6mm

* Typical values related to 1013 hPa, Ta = 22 °C, flow = 0.7 l / min for dry (not condensing) and clean sample gas.
Stated values exclude calibration gas tolerance.

** C.C : Internal Cross compensated by other gas

*** P.C : Pressure compensated

All rights reserved. Any logos and/or product names are trademarks of smartGAS. The reproduction, transfer, distribution or storage of information contained in this brochure in any form without the prior written consent of smartGAS is strictly prohibited. All specifications – technical included – are subject to change without notice. Depending on the application, the target gas and the measurement range the technical data may differ. No liability is accepted for any consequential losses, injury or damage resulting from the use of this document or from any omissions or errors herein. The data is given for guidance only. It does not constitute a specification or an offer for sale.

For more information, please visit www.smartgas.eu or contact us at sales@smartgas.eu

Please consult smartGAS sales for parts specified with other temperature and measurement ranges. At first initiation and depending on application and ambient conditions recalibration is recommended. Recurring cycles of recalibration are recommended.